


	Datafil:	23188MGB_C.doc	Säk-k:	Sida: 1(1)
	Titel:	Connecting a 23188/53188 with sensor and TCM 23408/53408 or TSM 23430/53430		
	Utfört:	Mikael Theorin	Datum:	2014-10-23
	Fastställt:		Datum:	
	Utgåva:	C	Telefon:	+46 8 747 67 00

The Ex barrier 23188/53188 can be used for one or two analog 4-20mA sensors like the 23417 in ATEX classed environments. Together with TCM 23408/53408 or TSM 23430/53430 it can be used for tanks containing fresh classed liquids or waste oil.

Always connect the sensors ground cable/point through the cable (23164/53464) to the ground connector in EX-barrier 23188/53188.



Analog level sensor 23417/53417 through EX-barrier 23188/53188 to a TCM (23408/53408) or TSM (23430/53430)

